

Model: LSX

LED Magnifier Lamp – 6 Diopter Instruction Sheet




With Care and attention to the following information your LSX magnifying lamp will give you years of satisfactory service.

General Features:

- The lamp head has a cover to protect the magnifying glass from the sunlight. Keep closed when not in use.
- Turn LED lighting ON/OFF with rocker switch on top of the head.
- For indoor use only – Do not use in wet areas.
- Clean with a soft dry cloth.
- If the supply cord is damaged it must be replaced by a qualified service agent to avoid hazard.
- Do not disassemble the magnifier head.

Mounting Lamp:

- The lamp is supplied with a clamp base for use on horizontal bench tops 13mm to 60mm thickness.
- Other lamp bases are available.
 - o Wall base LSM-3H
 - o Floor base LSM-12, LSM-11, LSM-8
 - o Bench top LSM-4



230 Volts, 50 Hz, 0.04A, Total Power = 10 Watts

Important:

The light source contained in this luminaire shall only be replaced by the manufacturer or his service agent or similar qualified person.

The lamp frame is not designed for use with the head below the height of the mounting. Fix the mounting base lower to prevent irreparable damage to the lamp base if using at a low height.

Gartner Superlux Ltd

Superlux Pty Ltd